

CYBEX

大腿伸展練習器

LEG EXTENSION



CYBEX®



1 設有限幅調節器
Range Limiting Device



2 靠背與座墊成100°
Back Pad is Angled 100° from
Seat Bottom



3 用者可調節起始臂的位置
Offset Input Arm provides for
Positioning

產品編號： Product Code：	11051 (11050 Total RLD)
機身及鐵餅重量： Machine weight with weight stack：	623磅(lb) / 283公斤(kg)
鐵餅配重重量： Weight stack：	305磅(lb) / 138公斤(kg)
尺寸(長x闊x高)： Dimensions(LxWxH)：	123x117x147厘米(cm)


開始 START

完成 FINISH



可鍛鍊部位：
肌四頭

Muscles trained：
Quadriceps



特點 Features

大腿伸展練習器 LEG EXTENSION

- **設有限幅調節器**，可調節合適的起始位置，並確保無論從那一個位置起始，阻力變化凸輪系統均能協調每個幅度，按照個人不同的極限及能力保持整個動作中力量的劃一。2項配置可供選擇：起始位置調節及全幅度調節。
- **靠背與座墊成100°**，有效減輕腿後肌所承受之張力。
- **機身設有平衡模組**，抵銷起始臂本身的重量，即使在最輕重量的情況下仍可保持一致的阻力。
- **用者可調節起始臂的位置**而不會影響膝部的起始角度。
- **隱蔽式鐵餅架結構**，並設有鐵餅緩衝器，保護用者及旁觀者以免受到鐵餅之碰撞或弄傷。設計已通過「美國材料試驗協會」及歐洲的標準，安全可靠。
- **第二代旋鈕式重量調節系統**，只需輕扭調節器，便可每次遞增或減5磅(2.5公斤)，無需推置或摘除，比傳統的推置式調節更安全簡捷。
- **油壓式背墊調節**，方便快捷，背墊及起始器均設有位置標記，讓用者每次使用設施時可依照標記調節至同一位置。
- **機身附有使用說明及操作指示圖。**
- **Range Limiting Device** maintains integrity of force curve while providing adjustment for appropriate starting position. Available in two configurations: Start RLD and Total RLD.
- **Back pad is angled 100°** from seat bottom to relieve hamstring pressure.
- **The Counterbalance system** provides consistent resistance at even the lowest weight selections.
- **Offset input arm provides for positioning** without affecting the starting angle of the knee.
- **Enclosed weight stacks** which comply with ASTM and EN standards help shield bystanders and users from inadvertent contact with the moving weight stack, creating a safer workout environment.
- **The Second Generation Twist Select Increment Weight System** allows user to adjust the weight 5 pounds (2.5kg) at a time with a simple turn of the knob - nothing to slide, drop or lose.
- **Gas spring assisted back pad** for easy adjustment. The seat back and input arm have position indicators to enable the user to perfectly duplicate their position on the machine each time they use it.
- **High contrast three-color placards** use straightforward language and pictures for easy-to-read instructions.